



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M3X20

Article number	24565.030.020
Brand	-
UBB	951353775210
UNSPSC	31161504
EAN	8715492635303
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

ISO	≈2009
DIN	963
NEN	≈2370
BS	≈4183
NF	≈E25-123
ASME	≈B18.6.7M

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	20
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

