



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M5X10

Article number	24565.050.010
Brand	-
UBB	950353621770
UNSPSC	31161504
EAN	8715492635419
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	10 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

DIN	963
NF	≈E25-123
BS	≈4183
ASME	≈B18.6.7M
ISO	≈2009
NEN	≈2370

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	10
n	1.2
P	0.8
t (min.)	1

Technical Drawing

