



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M5X20

Article number	24565.050.020
Brand	-
UBB	950353913581
UNSPSC	31161504
EAN	8715492635440
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NEN	≈2370
ISO	≈2009
BS	≈4183
DIN	963
NF	≈E25-123

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	20
n	1.2
P	0.8
t (min.)	1

Technical Drawing

