

Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M6X30



| | |
|----------------|---------------|
| Article number | 24565.060.030 |
| Brand | - |
| UBB | 950353621937 |
| UNSPSC | 31161504 |
| EAN | 8715492635563 |
| PKG. of 200 | Full Box Only |

Technical Parameters

| | |
|-------------------|------------------------------|
| Diameter (d-D) | M6 |
| Length (L) (mm) | 30 |
| Class | 4.8 |
| Driving features | Slotted |
| Head shape | Countersunk head |
| Material | Steel |
| Surface treatment | Zinc plated black passivated |
| Thread | Metric thread |

Standards

| | |
|------|-----------|
| DIN | 963 |
| NF | ≈E25-123 |
| BS | ≈4183 |
| ASME | ≈B18.6.7M |
| ISO | ≈2009 |

Technical Specification

| | |
|-------------------------|-----|
| Thread length (min.) | 28 |
| d_k (max.) | 11 |
| Full thread if $L \leq$ | 35 |
| k (max.) | 3 |
| n | 1.6 |
| P | 1 |
| t (min.) | 1.2 |

Technical Drawing

