

## Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M6X40



Article number	24565.060.040
Brand	-
UBB	951353774304
UNSPSC	31161504
EAN	8715492635570
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	40
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

### Standards

BS	≈4183
NF	≈E25-123
ISO	≈2009
ASME	≈B18.6.7M
DIN	963

### Technical Specification

Thread length (min.)	28
$d_k$ (max.)	11
Full thread if $L \leq$	35
$k$ (max.)	3
$n$	1.6
$P$	1
$t$ (min.)	1.2

### Technical Drawing

