



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M8X35

Article number	24565.080.035
Brand	-
UBB	950353914324
UNSPSC	31161504
EAN	8715492635679
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	35 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	963
NEN	≈2370
NF	≈E25-123
BS	≈4183
ISO	≈2009

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
Full thread if $L \leq$	40
k (max.)	4
L (mm)	35
n	2
P	1.25
t (min.)	1.6

Technical Drawing

