



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M8X40

Article number	24565.080.040
Brand	-
UBB	951353774973
UNSPSC	31161504
EAN	8715492635686
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

DIN	963
ISO	≈2009
NEN	≈2370
BS	≈4183
NF	≈E25-123
ASME	≈B18.6.7M

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
Full thread if $L \leq$	40
k (max.)	4
L (mm)	40
n	2
P	1.25
t (min.)	1.6

Technical Drawing

