



Slotted raised countersunk head screw DIN 964 Steel Plain 4.8 M5X35

Article number	24566.050.035
Brand	-
UBB	500648243573
UNSPSC	31161504
EAN	8717077226999
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	35 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	964
BS	≈4183
ISO	≈2010
NEN	≈2371
ASME	≈B18.6.7M
NF	≈E25-124

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
f ≈	1.25
Full thread if L ≤	30
k (max.)	2.5
L (mm)	35
n	1.2
P	0.8
t (min.)	2

Technical Drawing

