



Cross recessed countersunk head screw DIN 965 A-H Steel Plain 4.8 M4X8

Article number	24569.040.008
Brand	-
UBB	500648244720
UNSPSC	31161504
EAN	8717077227118
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M4
Length	8 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Plain
Thread	Metric thread

Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	8
No. cross recess	2
P	0.7

Technical Drawing

