



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M3X8

Article number	24570.030.008
Brand	-
UBB	950353147495
UNSPSC	31161504
EAN	8715492635860
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	8 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-124
DIN	964
ASME	≈B18.6.7M
BS	≈4183
NEN	≈2371
ISO	≈2010

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	8
n	0.8
P	0.5
t (min.)	1.2

Technical Drawing

