



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M3X10

Article number	24570.030.010
Brand	-
UBB	950353147560
UNSPSC	31161504
EAN	8715492635877
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	10 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	964
ISO	≈2010
BS	≈4183
NEN	≈2371
NF	≈E25-124

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	10
n	0.8
P	0.5
t (min.)	1.2

Technical Drawing

