

Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M3X12



Article number	24570.030.012
Brand	-
UBB	950353147644
UNSPSC	31161504
EAN	8715492635884
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	12
Class	4.8
Driving features	Slotted
Head shape	Raised countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	964
ISO	≈2010
NF	≈E25-124
ASME	≈B18.6.7M
BS	≈4183

Technical Specification

Thread length (min.)	19
d_k (max.)	5.6
$f \approx$	0.75
Full thread if $L \leq$	22
k (max.)	1.65
n	0.8
P	0.50
t (min.)	1.2

Technical Drawing

