



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M3X25

Article number	24570.030.025
Brand	-
UBB	950353147982
UNSPSC	31161504
EAN	8715492635921
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	964
NF	≈E25-124
BS	≈4183
ASME	≈B18.6.7M
ISO	≈2010
NEN	≈2371

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	25
n	0.8
P	0.5
t (min.)	1.2

Technical Drawing

