

Slotted raised countersunk head screw DIN 964 A Steel Zinc plated 4.8 M4X8



Article No.	24570.040.008
Brand	-
UBB	950353148303
UNSPSC	31161504
EAN	8715492635990
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M4
Length (L) (mm)	8
Class	4.8
Driving features	Slotted
Head shape	Raised countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-124
BS	4183
ASME	B18.6.7M
DIN	964 A
ISO	2010

Technical Specification

d_k	7.5
$f \approx$	1
Full thread if $L \leq$	25
k (max.)	2.2
n	1
P	0.70

Technical Drawing

