



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M4X16

Article number	24570.040.016
Brand	-
UBB	950353148634
UNSPSC	31161504
EAN	8715492636027
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
ASME	≈B18.6.7M
DIN	964
NEN	≈2371
ISO	≈2010
NF	≈E25-124

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	16
n	1
P	0.7
t (min.)	1.6

Technical Drawing

