



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M4X20

Article number	24570.040.020
Brand	-
UBB	950353148717
UNSPSC	31161504
EAN	8715492636034
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	964
NF	≈E25-124
ASME	≈B18.6.7M
BS	≈4183
ISO	≈2010
NEN	≈2371

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	20
n	1
P	0.7
t (min.)	1.6

Technical Drawing

