



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M4X30

Article number	24570.040.030
Brand	-
UBB	950353148972
UNSPSC	31161504
EAN	8715492636058
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-124
NEN	≈2371
DIN	964
BS	≈4183
ASME	≈B18.6.7M
ISO	≈2010

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	30
n	1
P	0.7
t (min.)	1.6

Technical Drawing

