

Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M4X40



Article number 24570.040.040

Brand -

UBB 950353149053

UNSPSC 31161504

EAN 8715492636072

PKG. of 200 Full Box Only

Technical Parameters

Diameter (d-D)	M4
Length (L) (mm)	40
Class	4.8
Driving features	Slotted
Head shape	Raised countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	964
BS	≈4183
ISO	≈2010
NF	≈E25-124

Technical Specification

Thread length (min.)	22
d_k (max.)	7.5
$f \approx$	1
Full thread if $L \leq$	25
k (max.)	2.2
n	1
P	0.70
t (min.)	1.6

Technical Drawing

