



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M5X20

Article number	24570.050.020
Brand	-
UBB	950353149707
UNSPSC	31161504
EAN	8715492636164
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
NEN	≈2371
DIN	964
ISO	≈2010
NF	≈E25-124

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
f ≈	1.25
Full thread if L ≤	30
k (max.)	2.5
L (mm)	20
n	1.2
P	0.8
t (min.)	2

Technical Drawing

