

## Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M5X30



Article number 24570.050.030

Brand -

UBB 950353149962

UNSPSC 31161504

EAN 8715492636188

PKG. of 500 Full Box Only

### Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	30
Class	4.8
Driving features	Slotted
Head shape	Raised countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

DIN	964
BS	≈4183
NF	≈E25-124
ISO	≈2010
ASME	≈B18.6.7M

### Technical Specification

Thread length (min.)	25
$d_k$ (max.)	9.2
$f \approx$	1.25
Full thread if $L \leq$	30
$k$ (max.)	2.5
$n$	1.2
$P$	0.80
$t$ (min.)	2

### Technical Drawing

