



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M5X35

Article number	24570.050.035
Brand	-
UBB	950353335330
UNSPSC	31161504
EAN	8715492636195
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	35 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-124
DIN	964
ASME	≈B18.6.7M
BS	≈4183
ISO	≈2010
NEN	≈2371

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
f ≈	1.25
Full thread if L ≤	30
k (max.)	2.5
L (mm)	35
n	1.2
P	0.8
t (min.)	2

Technical Drawing

