



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M5X40

Article number	24570.050.040
Brand	-
UBB	950353150192
UNSPSC	31161504
EAN	8715492636201
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-124
ISO	≈2010
NEN	≈2371
ASME	≈B18.6.7M
BS	≈4183
DIN	964

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
f ≈	1.25
Full thread if L ≤	30
k (max.)	2.5
L (mm)	40
n	1.2
P	0.8
t (min.)	2

Technical Drawing

