

Slotted raised countersunk head screw DIN 964 A Steel Zinc plated 4.8 M5X60



Article No.	24570.050.060
Brand	-
UBB	950353150432
UNSPSC	31161504
EAN	8715492636232
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	60
Class	4.8
Driving features	Slotted
Head shape	Raised countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.6.7M
NF	E25-124
DIN	964 A
ISO	2010
BS	4183

Technical Specification

d_k	9.2
$f \approx$	1.25
Full thread if $L \leq$	30
k (max.)	2.5
n	1.2
P	0.80

Technical Drawing

