



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M6X10

Article number	24570.060.010
Brand	-
UBB	950353150507
UNSPSC	31161504
EAN	8715492636256
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	10 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
DIN	964
NEN	≈2371
ASME	≈B18.6.7M
NF	≈E25-124
ISO	≈2010

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	10
n	1.6
P	1
t (min.)	2.4

Technical Drawing

