



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M6X16

Article number	24570.060.016
Brand	-
UBB	950353150762
UNSPSC	31161504
EAN	8715492636270
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	964
NEN	≈2371
NF	≈E25-124
ASME	≈B18.6.7M
ISO	≈2010
BS	≈4183

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	16
n	1.6
P	1
t (min.)	2.4

Technical Drawing

