



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M6X35

Article number	24570.060.035
Brand	-
UBB	950353151182
UNSPSC	31161504
EAN	8715492636317
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	35 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-124
DIN	964
ISO	≈2010
NEN	≈2371
BS	≈4183
ASME	≈B18.6.7M

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	35
n	1.6
P	1
t (min.)	2.4

Technical Drawing

