



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M6X40

Article number	24570.060.040
Brand	-
UBB	950353151265
UNSPSC	31161504
EAN	8715492636324
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
NEN	≈2371
DIN	964
ISO	≈2010
NF	≈E25-124

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	40
n	1.6
P	1
t (min.)	2.4

Technical Drawing

