



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M8X20

Article number	24570.080.020
Brand	-
UBB	950353151679
UNSPSC	31161504
EAN	8715492636379
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2010
ASME	≈B18.6.7M
NEN	≈2371
DIN	964
BS	≈4183
NF	≈E25-124

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
f ≈	2
Full thread if L ≤	40
k (max.)	4
L (mm)	20
n	2
P	1.25
t (min.)	3.2

Technical Drawing

