

Slotted raised countersunk head screw DIN 964 A Steel Zinc plated 4.8 M8X50



Article No.	24570.080.050
Brand	-
UBB	950353152099
UNSPSC	31161504
EAN	8715492636430
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M8
Length (L) (mm)	50
Class	4.8
Driving features	Slotted
Head shape	Raised countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	2010
BS	4183
NF	E25-124
ASME	B18.6.7M
DIN	964 A

Technical Specification

d_k	14.5
$f \approx$	2
Full thread if $L \leq$	40
k (max.)	4
n	2
P	1.25

Technical Drawing

