



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M8X60

Article number	24570.080.060
Brand	-
UBB	950353152172
UNSPSC	31161504
EAN	8715492636447
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NF	≈E25-124
ISO	≈2010
BS	≈4183
DIN	964
NEN	≈2371

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
f ≈	2
Full thread if L ≤	40
k (max.)	4
L (mm)	60
n	2
P	1.25
t (min.)	3.2

Technical Drawing

