



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M3X6

Article number	24640.030.006
Brand	-
UBB	950353152412
UNSPSC	31161504
EAN	8715492636966
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	6 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

BS	≈4183
DIN	85
NF	≈E25-128
ASME	≈B18.6.7M
NEN	≈1603
ISO	≈1580

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	6
Full thread if $L \leq$	30
k (max.)	1.8
L (mm)	6
n	0.8
P	0.5
t (min.)	0.7

Technical Drawing

