

## Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M3X8



Article number	24640.030.008
Brand	-
UBB	950353152586
UNSPSC	31161504
EAN	8715492636973
PKG. of 500	Full Box Only

### Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	8
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

BS	≈4183
DIN	85
ISO	≈1580
NF	≈E25-128
ASME	≈B18.6.7M

### Technical Specification

Thread length (min.)	25
$d_k$ (max.)	6
Full thread if $L \leq$	30
$k$ (max.)	1.8
$n$	0.8
$P$	0.50
$t$ (min.)	0.7

### Technical Drawing

