

Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M3X10



| | |
|----------------|---------------|
| Article number | 24640.030.010 |
| Brand | - |
| UBB | 950353152669 |
| UNSPSC | 31161504 |
| EAN | 8715492636980 |
| PKG. of 500 | Full Box Only |

Technical Parameters

| | |
|-------------------|---------------|
| Diameter (d-D) | M3 |
| Length (L) (mm) | 10 |
| Class | 4.8 |
| Driving features | Slotted |
| Head shape | Pan head |
| Material | Steel |
| Surface treatment | Zinc plated |
| Thread | Metric thread |

Standards

| | |
|------|-----------|
| BS | ≈4183 |
| NF | ≈E25-128 |
| ISO | ≈1580 |
| ASME | ≈B18.6.7M |
| DIN | 85 |

Technical Specification

| | |
|-------------------------|------|
| Thread length (min.) | 25 |
| d_k (max.) | 6 |
| Full thread if $L \leq$ | 30 |
| k (max.) | 1.8 |
| n | 0.8 |
| P | 0.50 |
| t (min.) | 0.7 |

Technical Drawing

