

Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M3X20



Article number 24640.030.020

Brand -

UBB 950353152909

UNSPSC 31161504

EAN 8715492637031

PKG. of 500 Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	20
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NF	≈E25-128
ISO	≈1580
DIN	85
BS	≈4183

Technical Specification

Thread length (min.)	25
d_k (max.)	6
Full thread if $L \leq$	30
k (max.)	1.8
n	0.8
P	0.50
t (min.)	0.7

Technical Drawing

