



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M3X25

Article number	24640.030.025
Brand	-
UBB	950353153089
UNSPSC	31161504
EAN	8715492637048
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

ASME	≈B18.6.7M
ISO	≈1580
DIN	85
NF	≈E25-128
BS	≈4183
NEN	≈1603

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	6
Full thread if $L \leq$	30
k (max.)	1.8
L (mm)	25
n	0.8
P	0.5
t (min.)	0.7

Technical Drawing

