



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M4X12

Article number	24640.040.012
Brand	-
UBB	950353153659
UNSPSC	31161504
EAN	8715492637291
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	12 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

ISO	≈1580
NF	≈E25-128
BS	≈4183
DIN	85
NEN	≈1603
ASME	≈B18.6.7M

Technical Specification

d-D	M4
Thread length (min.)	38
dk (max.)	8
Full thread if $L \leq$	40
k (max.)	2.4
L (mm)	12
n	1.2
P	0.7
t (min.)	1

Technical Drawing

