



## Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M4X40

|                |               |
|----------------|---------------|
| Article number | 24640.040.040 |
| Brand          | -             |
| UBB            | 950353154152  |
| UNSPSC         | 31161504      |
| EAN            | 8715492637383 |
| PKG. of 500    | Full Box Only |

### Technical Parameters

|                   |                                                    |
|-------------------|----------------------------------------------------|
| Diameter          | M4                                                 |
| Length            | 40 mm                                              |
| Class             | 4.8                                                |
| Driving features  | Slotted                                            |
| Head shape        | Pan head                                           |
| Material          | Steel                                              |
| Surface treatment | Zinc plated                                        |
| Thread            | Metric thread                                      |
| Info              | N = Max. recom. static load (centr. tension) [kN]. |

### Standards

|      |           |
|------|-----------|
| DIN  | 85        |
| BS   | ≈4183     |
| ISO  | ≈1580     |
| NF   | ≈E25-128  |
| NEN  | ≈1603     |
| ASME | ≈B18.6.7M |

### Technical Specification

|                         |     |
|-------------------------|-----|
| d-D                     | M4  |
| Thread length (min.)    | 38  |
| dk (max.)               | 8   |
| Full thread if $L \leq$ | 40  |
| k (max.)                | 2.4 |
| L (mm)                  | 40  |
| n                       | 1.2 |
| P                       | 0.7 |
| t (min.)                | 1   |

### Technical Drawing

