



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M5X16

Article number	24640.050.016
Brand	-
UBB	950353154566
UNSPSC	31161504
EAN	8715492637512
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

ASME	≈B18.6.7M
NEN	≈1603
NF	≈E25-128
BS	≈4183
DIN	85
ISO	≈1580

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	10
Full thread if $L \leq$	40
k (max.)	3
L (mm)	16
n	1.2
P	0.8
t (min.)	1.2

Technical Drawing

