



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M5X50

Article number	24640.050.050
Brand	-
UBB	950353155068
UNSPSC	31161504
EAN	8715492637598
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

ASME	≈B18.6.7M
DIN	85
ISO	≈1580
NF	≈E25-128
BS	≈4183
NEN	≈1603

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	10
Full thread if $L \leq$	40
k (max.)	3
L (mm)	50
n	1.2
P	0.8
t (min.)	1.2

Technical Drawing

