



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M6X30

Article number	24640.060.030
Brand	-
UBB	950353155712
UNSPSC	31161504
EAN	8715492637710
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

BS	≈4183
NF	≈E25-128
ASME	≈B18.6.7M
NEN	≈1603
ISO	≈1580
DIN	85

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	12
Full thread if L ≤	40
k (max.)	3.6
L (mm)	30
n	1.6
P	1
t (min.)	1.4

Technical Drawing

