



Slotted pan head screw DIN 85 Steel Zinc plated 4.8 M8X20

Article number	24640.080.020
Brand	-
UBB	950353636620
UNSPSC	31161504
EAN	8715492637833
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	N = Max. recom. static load (centr. tension) [kN].

Standards

NF	≈E25-128
NEN	≈1603
BS	≈4183
ASME	≈B18.6.7M
ISO	≈1580
DIN	85

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	16
Full thread if $L \leq$	40
k (max.)	4.8
L (mm)	20
n	2
P	1.25
t (min.)	1.9

Technical Drawing

