



Double slotted mushroom head screw NF ≈E25-129 Steel Zinc plated 4.8 M8X30

Article number	24650.080.030
Brand	-
UBB	951353572344
UNSPSC	31161504
EAN	8715492638748
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M8
Length (L) (mm)	30
Info	M6 Application in combination with pointed nuts in boxes and cabinets.
Class	4.8
Driving features	Slotted
Head shape	Button head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-129
----	----------

Technical Specification

d_k (max.)	20
k (max.)	4.4
n	2
P	1.25

Technical Drawing

