

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 large pack M2X5

Article number	24660.020.005
Brand	-
UBB	950353515501
UNSPSC	31161504
EAN	8715492638960
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M2
Length	5 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	large pack

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	4
Full thread if $L \leq$	18
k	1.6
L (mm)	5
No. cross recess	1
P	0.4

Technical Drawing

