

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 large pack M3X25

| | |
|----------------|---------------|
| Article number | 24660.030.025 |
| Brand | - |
| UBB | 950353157619 |
| UNSPSC | 31161504 |
| EAN | 8715492639240 |
| PKG. of 1000 | Full Box Only |

Technical Parameters

| | |
|-------------------|--------------------|
| Diameter | M3 |
| Length | 25 mm |
| Class | 4.8 |
| Driving features | Phillips |
| Head shape | Raised cheese head |
| Material | Steel |
| Surface treatment | Zinc plated |
| Thread | Metric thread |
| Info | large pack |

Standards

| | |
|-----|-------|
| DIN | 7985 |
| ISO | ≈7045 |

Technical Specification

| | |
|-------------------------|-----|
| d-D | M3 |
| Thread length (min.) | 19 |
| dk (max.) | 6 |
| Full thread if $L \leq$ | 20 |
| k | 2.4 |
| L (mm) | 25 |
| No. cross recess | 1 |
| P | 0.5 |

Technical Drawing

