

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 large pack M6X16

Article number	24660.060.016
Brand	-
UBB	950353160589
UNSPSC	31161504
EAN	8715492639752
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M6
Length	16 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	large pack

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	12
Full thread if $L \leq$	35
k	4.6
L (mm)	16
No. cross recess	3
P	1

Technical Drawing

