

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated 4.8 large pack M8X20

Article number	24660.080.020
Brand	-
UBB	950353161652
UNSPSC	31161504
EAN	8715492639875
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M8
Length	20 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	large pack

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	16
Full thread if $L \leq$	40
k	6
L (mm)	20
No. cross recess	4
P	1.25

Technical Drawing

