



Cross recessed raised cheese head screw Pozidriv DIN 7985-Z Steel Zinc plated 4.8 M3X4

Article number	24662.030.004
Brand	-
UBB	500645205005
UNSPSC	31161504
EAN	8717077071131
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M3
Length	4 mm
Class	4.8
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	6
Full thread if $L \leq$	20
k	2.4
L (mm)	4
No. cross recess	1
P	0.5

Technical Drawing

