



Cross recessed raised cheese head screw Pozidriv DIN 7985-Z Steel Zinc plated 4.8 M3X20

Article number	24662.030.020
Brand	-
UBB	950353752609
UNSPSC	31161504
EAN	8715492640079
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	4.8
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	6
Full thread if $L \leq$	20
k	2.4
L (mm)	20
No. cross recess	1
P	0.5

Technical Drawing

