



Cross recessed raised cheese head screw Pozidriv DIN 7985-Z Steel Zinc plated 4.8 M4X25

Article number	24662.040.025
Brand	-
UBB	950353753516
UNSPSC	31161504
EAN	8715492640185
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M4
Length	25 mm
Class	4.8
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	8
Full thread if $L \leq$	25
k	3.1
L (mm)	25
No. cross recess	2
P	0.7

Technical Drawing

