



Cross recessed raised cheese head screw Pozidriv DIN 7985-Z Steel Zinc plated 4.8 M8X30

Article number	24662.080.030
Brand	-
UBB	950353962745
UNSPSC	31161504
EAN	8715492640475
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M8
Length	30 mm
Class	4.8
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	16
Full thread if $L \leq$	40
k	6
L (mm)	30
No. cross recess	4
P	1.25

Technical Drawing

